

Premium Cast 4BAY Light


T: +1 713.783.2367

E: <u>business@efficientpowertech.com</u> www.efficientpowertech.com

EFFICIENT POWER TECH
Houston Texas

Parameters







WATTAGE 50/100/150/200W


DRIVER MEANWELL

RATED VOLTAGE AC 100-240V, 50/60Hz

POWER FACTOR >0.95

HEAT SINK ALUMINIUM COOLING FIN

OPERATING TEMP -40°F~104°F





UVC Three-dimensional light field simulation

Size: 33ft (length) x 33ft (width) x 19.5 (height)




Time: 30min






	Position(X,Y)	Sterilization rate		
а	0, 0	92.0567%		
b	100, -100	93.6904%		
С	200, -200	87.4107%		
d	300 -300	74.8811%		
е	400, -400	60.1893%		
f	500, -500	36.9043%		

Time: 30min



	Position(X,Y)	Sterilization rate		
а	0, 0	99.4988%		
b	100, -100	99.6019%		
С	200, -200	98.7411%		
d	300 -300	93.6904%		
е	400, -400	80.0474%		
f	500, -500	60.1893%		

Time: 30min




	Position(X,Y)	Sterilization rate		
а	0, 0	99.9975%		
b	100, -100	99.9984%		
С	200, -200	99.9842%		
d	300 -300	99.6019%		
е	400, -400	96.0189%		
f	500, -500	84.1511%		


UVC Three-dimensional light field simulation

Size: 39.5ft (length) x 39.5ft (width) x 24.5ft (height)











	Position(X,Y)	Sterilization rate		
а	0, 0	96.8377%		
b	120, -120	96.8377%		
С	240, -240	94.9881%		
d	360, -360	84.1511%		
е	480, -480	68.3772%		
f	600, -600	49.8813%		

Time: 120min



	Position(X,Y)	Sterilization rate		
а	0, 0	99.8741%		
b	120, -120	99.9206%		
С	240, -240	99.6838%		
d	360, -360	98.0047%		
е	480, -480	90.0000%		
f	600, -600	74.8811%		

Time: 180min



	Position(X,Y)	Sterilization rate		
	POSITION(X,1)	Steriiization rat		
а	0, 0	99.9960%		
b	120, -120	99.9975%		
С	240, -240	99.9842%		
d	360, -360	99.6838%		
е	480, -480	96.0189%		
f	600, -600	87.4107%		

Ultraviolet C 'The Truly Effective Purification Wavelength'




200-280nm. The non visible precision UVC chip used in this product.



390-400nm. The purple visible UVA chip used in imitation pseudo products with no purification properties.







HOW UVC WORKS?

Ultra-Violet (UV) light is invisible to human eyes. It can be subdivided into three categories: UVA, UVB and UVC. UV-A from 320 to 400 nm UV-B from 280 to 320 nm UV-C from 200 to 280 nm.


UVC radiation is known to break the DNA of bacteria, viruses and spores. As a result, they are rendered harmless.


UV radiation can be used for multiple purposes in water and air treatment, but is primarily employed as a disinfection process that inactivates micro-organisms without chemicals. For other applications, UV is used for the removal of organic and inorganic chemicals, including chlorine, chloramines, ozone and Total Organic Carbon (TOC) emerging contaminants.


UVC radiation has been proven to be effective against waterborne pathogenic microorganisms including those responsible for cholera, hepatitis, polio, typhoid, giardia, cryptosporidium and many other bacterial, viral and parasitic diseases.


UVC disinfection is complementary to Chlorine disinfection: it deactivates organisms that are resistant to Chlorine such as giardia and cryptosporidium.













Silent Guardian

Highly efficient non-chlorinated bactericidal, no chemical drugs residue











Stadium

Supermarket

Station

Application



Hospital



Airport



Laundry




Warehou




Factory


Manual Control



Work pattern





1. Switch the light on, start with 10 seconds alarm, please leave immediately!



2. The purification light start working, and automatically turned off after 4 hours (optional).

Setting purification time







Please rotate ② to set timming, and rotate ① to set the timming percentage.
For example: set the time to 4 hours, please rotate ② to "10h" and ① to 40%.



Packaging and Size





Model	Net Weight	Size of Box	Weight of Carton	Size of Carton	Gross Weight of Carton	PCS /Carton
50W	5.30kg±5%	47*46*15cm	6.10kg±5%	50*49*66cm	26.50KG±5%	4
100W	5.35kg±5%	47*46*15cm	6.15kg±5%	50*49*66cm	26.66KG±5%	4
150W	5.45kg±5%	47*46*15cm	6.25kg±5%	50*49* <mark>66cm</mark>	26.70KG±5%	4
200W	5.70kg±5%	47*46*15cm	6.50kg±5%	50*49*66cm	26.90KG±5%	4

